

Stereo zoom microscope KERN OZL-46



OZL 464
With standard stand



OZL 465
With ring illumination



OZL 467
With handle

LAB LINE

The flexible, affordable all-rounder with zoom function for schools, training companies, inspection authorities and laboratories

Features

- The products in the KERN OZL-46 series are stereo zoom microscopes, which will impress you with their quality, easy handling, flexibility as well as their stability and economical price
- The LED reflected and transmitted illumination included as standard guarantees the very best illumination of your sample
- The highlight of the OZL 465/OZL 466 is the strong, continuously dimmable, integrated LED ring illumination in the objective housing, which ensures uniform, shadow-free illumination. An LED transmitted light variant is also included
- As well as excellent optical characteristics and their large working surface, these models offer the highest level of comfort in this class – ideal for training companies, workshops as well as assembly and repair workstations, e.g. in the electronics industry
- The zoom objective offers you continuous magnification from 7×–45×
- The KERN OZL-46 series is available as a binocular or trinocular version
- The pillar stand offers you the highest level of flexibility and the freedom to remove the microscope head and to integrate it into other modular systems, for example into a universal stand
- With its integrated handle as well as its stable arm curved stand, the KERN OZL 467/OZL 468 has been specially developed for schools and workshops
- A large selection of eyepieces, external illumination units as well as auxiliary objectives are available as accessories
- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- A C-mount adapter is required to connect a camera to the trinocular version. You can select this adapter from the following model outfit list
- Please find detailed information in the following model outfit list

Scope of application

- In vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

Applications/Samples

- Samples with focus on three-dimensional impression, zoom with variable magnification (depth, thickness), e.g. insects, seeds, circuit boards, components

Technical data

- Optical system: Greenough optics
- Brightness adjustable (separate)
- Tube 45° inclined
- Magnification ratio: 6,4:1
- Light distribution OZL 464/466/468: 100:0
- Interpupillary distance 55 – 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 300×240×420 mm
- Net weight approx. 4 kg

STANDARD



Model	Standard configuration					
	Tube	Eyepiece	Field of view mm	Objective Zoom	Stand	Illumination
KERN						
OZL 463	Binocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)
OZL 464	Trinocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)
OZL 465	Binocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)
OZL 466	Trinocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)
OZL 467	Binocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Arm curved	3 W LED (incident); 3 W LED (transmitted)
OZL 468	Trinocular	HWF 10×/ø 20 mm	ø 28,6 – 4,4	0,7× – 4,5×	Arm curved	3 W LED (incident); 3 W LED (transmitted)

































Stereo zoom microscope KERN OZL-46

Eyepiece	Magnification	Specifications – Objectives					
		Standard	Auxiliary objectives				
			1,0×	0,5×	0,75×	1,5×	2,0×
HSWF 10×	Total magnification	7× – 45×	3,5× – 22,5×	5,3× – 33,8×	10,5× – 67,5×	14× – 90×	
	Field of view mm	∅ 28,6 – 4,4	∅ 57,1 – 8,9	∅ 38,1 – 5,9	∅ 19 – 3	∅ 14,3 – 2,2	
HWF 15×	Total magnification	10,5× – 67,5×	5,3× – 33,8×	7,9× – 50,6×	15,5× – 101,3×	21× – 135×	
	Field of view mm	∅ 21,4 – 3,3	∅ 42,9 – 6,7	∅ 28,5 – 4,4	∅ 14,3 – 2,2	∅ 10,7 – 1,7	
HSWF 20×	Total magnification	14× – 90×	7× – 45×	10,5× – 67,5×	21× – 135×	28× – 180×	
	Field of view mm	∅ 14,3 – 2,2	∅ 28,6 – 4,4	∅ 19,1 – 2,9	∅ 9,5 – 1,5	∅ 7,1 – 1,1	
HWF 25×	Total magnification	17,5× – 112,5×	8,8× – 56,3×	13,1× – 91,9×	26,3× – 168,8×	35× – 225×	
	Field of view mm	∅ 12,9 – 2,0	∅ 25,7 – 4,0	∅ 17,2 – 2,7	∅ 8,6 – 1,3	∅ 6,4 – 1,0	
Working distance		105 mm	177 mm	120 mm	47 mm	26 mm	
Maximum sample height		140 mm	35 mm	80 mm	165 mm	185 mm	

Model outfit		Model KERN						Order number
		OZL 463	OZL 464	OZL 465	OZL 466	OZL 467	OZL 468	
Eyepieces (30,0 mm)	HWF 10×/∅ 20 mm	✓✓	✓✓	✓✓	✓✓	✓✓	✓✓	OZB-A4631
	HSWF 15×/∅ 15 mm	○ ○	○ ○	○ ○	○ ○	○ ○	○ ○	OZB-A4632
	HWF 20×/∅ 10 mm	○ ○	○ ○	○ ○	○ ○	○ ○	○ ○	OZB-A4633
	HSWF 25×/∅ 9 mm	○ ○	○ ○	○ ○	○ ○	○ ○	○ ○	OZB-A4634
Auxiliary objectives	0,5×	○	○			○	○	OZB-A4641
	0,75×	○	○			○	○	OZB-A4644
	1,5×	○	○			○	○	OZB-A4642
	2,0×	○	○			○	○	OZB-A4643
	Soldering protection lens	○	○			○	○	OZB-A4645
C-Mount	1× (focus adjustable)		✓		✓		✓	OZB-A4809
	0,3× (focus adjustable)		○		○		○	OZB-A4810
	0,5× (focus adjustable)		○		○		○	OZB-A4811
Eyepiece camera adapter	1,0×; for fitting an eyepiece camera to the trinocular connection of the microscope		○		○		○	OZB-A4863
Stand	Pillar style, with 3 W-LED illumination (transmitted + incident)	✓	✓					
	Pillar style, with 3 W-LED illumination (transmitted)			✓	✓			
	Arm curved, incl. handle, with 3 W-LED illumination (transmitted + incident)					✓	✓	
Ring illumination	Integrated into the microscope head as incident illumination			✓	✓			
Stage plate	Frosted glass/∅ 95 mm	✓	✓	✓	✓	✓	✓	OZB-A4670
	Black-white/∅ 95 mm	✓	✓	✓	✓	✓	✓	OZB-A4806
External illumination	Please find the information about external illumination units in the catalogue on page 83 and on the internet							

✓ = Included with delivery

○ = Option

- 
360° rotatable microscope head
- 
Monocular Microscope
 For the inspection with one eye
- 
Binocular Microscope
 For the inspection with both eyes
- 
Trinocular Microscope
 For the inspection with both eyes and the additional option for the connection of a camera
- 
Abbe Condenser
 With high numerical aperture for the concentration and the focusing of light
- 
Halogen illumination
 For pictures bright and rich in contrast
- 
LED illumination
 Cold, energy-saving and especially long-life illumination
- 
Incident illumination
 For non-transparent objects
- 
Transmitting illumination
 For transparent objects
- 
Fluorescence illumination
 For stereomicroscopes
- 
Fluorescence illumination for compound microscopes
 With 100 W mercury lamp and filter
- 
Fluorescence illumination for compound microscopes
 With 3 W LED illumination and filter
- 
Phase contrast unit
 For a higher contrast
- 
Darkfield condenser/unit
 For a higher contrast due to indirect illumination
- 
Polarising unit
 To polarise the light
- 
Infinity system
 Infinity corrected optical system
- 
Zoom magnification
 For stereomicroscopes
- 
Auto-focus
 For automatic control of the focus level
- 
Parallel optical system
 For stereomicroscopes, enables fatigue-proof working
- 
Integrated scale
 In the eyepiece
- 
SD card
 For data storage
- 
USB 2.0 digital camera
 For direct transmitting of the picture to a PC
- 
USB 3.0 digital camera
 For direct transmitting of the picture to a PC
- 
WiFi data interface:
 For transmitting of the picture to a mobile display device
- 
HDMI digital camera
 For direct transmitting of the picture to a display device
- 
PC software
 To transfer the measurements from the device to a PC.
- 
Automatic temperature compensation
 For measurements between 10 °C and 30 °C
- 
Protection against dust and water splashes IPxx:
 The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013
- 
Battery operation
 Ready for battery operation. The battery type is specified for each device.
- 
Battery operation rechargeable
 Prepared for a rechargeable battery operation
- 
Plug-in power supply
 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
- 
Integrated power supply unit
 Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
- 
Package shipment
 The time required to manufacture the product internally is shown in days in the pictogram.

ABBREVIATIONS

- C-Mount** Adapter for the connection of a camera to a trinocular microscope
- FPS** Frames per second
- H(S)WF** High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)
- LWD** Long Working Distance
- N.A.** Numerical Aperture
- SLR camera** Single-Lens Reflex camera
- SWF** Super Wide Field (Field number at least \varnothing 23 mm for 10 \times eyepiece)
- W.D.** Working Distance
- WF** Wide Field (Field number up to \varnothing 22 mm for 10 \times eyepiece)